



Three-leg extractor, Type: 5



Order data

| | |
|--------------|---------------|
| Order number | 880130 5 |
| GTIN | 4021176075421 |
| Item class | 83U |

Description

Version:

With reversible extraction legs (**for external and internal extraction**). Extraction legs adjustable on cross beam for different workpiece \varnothing . Extraction legs and cross beam of high-quality tool steel; sturdy double-ended spindle (ball end and point end).

Application:

Universally applicable for extracting bearings, discs, gear wheels etc. On model 880100 size 5 the depth of reach can be extended from 400 mm (normal) up to 700 mm by adjusting the legs.

Technical description

| | |
|-------------------------|--------------|
| Depth of reach up to | 200 mm |
| External clamping range | 190 - 520 mm |
| Internal capacity | 280 - 600 mm |
| Power | 20 t |
| maximum torque | 650 Nm |
| Number of hooks | 3 |

| | |
|------------------------|---------------------|
| External hexagon drive | 41 mm |
| Weight | 22.72 kg |
| Type of product | Three-leg extractor |

Accessories

| | |
|---|--------------|
| Spare extractor legs (3 pieces) Type / Clamping depth 3/200 mm | 880220 3/200 |
| Extended extractor legs (3 pieces) Type / Clamping depth 4/500 mm | 880320 4/500 |
| Pair of spare extractor legs Type / Clamping depth 3/200 mm | 880200 3/200 |
| Hydraulic pressure spindle Type 2 | 880170 2 |