

Garant
"5 in 1" drilling and turning tool 1.5×D, left-hand, Ø DC: 11mm

Order data

Order number	268464 11
GTIN	4045197975218
Item class	21X

Description
Version:

With internal cooling.

Plain shank.

Application:

Face turning, longitudinal turning, drilling, internal longitudinal turning, countersinking.

Note:

- **Choose corner radii as large as possible.**
- **Always use internal cooling for drilling (at least 5 bar).**

Technical description

Nominal Ø D	11 mm
Pack of insert screws	269028 32
Reach L ₁	16.5 mm
Bore Ø tolerance D	0/+0.27 mm
Indexable insert No. 268472 – 268496	WCHX 0602..
Shank Ø D _s	16 mm
Overall length L	100 mm
Application type	left-hand
Through-coolant	yes
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500