



Two-leg extractor, Type: 20



Order data

Order number	880100 20
GTIN	4021176010088
Item class	83U

Description

Version:

With reversible extraction legs (**for external and internal extraction**). Extraction legs adjustable on cross beam for different workpiece \varnothing . Extraction legs and cross beam of high-quality tool steel; sturdy double-ended spindle (ball end and point end).

Application:

Universally applicable for extracting bearings, discs, gear wheels etc. On model 880100 size 5 the depth of reach can be extended from 400 mm (normal) up to 700 mm by adjusting the legs.

Technical description

Depth of reach up to	150 mm
Internal capacity	100 - 260 mm
Power	6 t
External clamping range	40 - 200 mm
External hexagon drive	22 mm
Number of hooks	2

maximum torque	150 Nm
Weight	3.22 kg
Type of product	Two-leg extractor

Accessories

Pair of spare extractor legs Type / Clamping depth 2/150 mm	880200 2/150
Pair of extended extractor legs Type / Clamping depth 2/300 mm	880300 2/300
Spare extractor legs (3 pieces) Type / Clamping depth 2/150 mm	880220 2/150
Spare pressure spindle Type 2	880150 2