

## ROLLER

### Anaconda WB chain clamp for pipes, Capacity for pipes up to: 1/8-6 inch

#### Order data

Order number	868650 1/8-6
GTIN	95691362735
Item class	83S

#### Description

##### Version:

Sturdy chain clamp for pipes for attaching to a workbench. For easy secure clamping of pipes using special serrated Vee-shaped clamping jaws and a sturdy clamping chain with a quick-release fastener.

- **Sturdy distortion-free cast design of the baseplate, with integral chain clamp vice, pipe support and bending machine.**
- **Specially serrated and hardened double vice jaws, easily exchanged, Vee-shaped for secure clamping of pipes.**
- **Clamping chain with sturdy chain links, easily clamped with quick-release fastener and trapezoidal thread spindle.**
- **For attachment to a workbench – please ensure compliance with the workbench load capacity.**

##### Application:

Secure clamping of pipes and solid materials, 1/8 inch – 6 inches (10 – 165 mm).

##### Note:

Adjustable material stand No. 919904 and workbenches from No. 921001 can be found in the Workstations and Storage catalogue.

Jaw capacity: 6 - 150 mm

Working area: 648 cm<sup>2</sup>

Weight: 21 kg

#### Technical description

maximum loading	kg
Type of product	

