

**Cordless 2-speed drill / driver, Type: 71132064****Order data**

Order number	070205 71132064
GTIN	4014586885568
Item class	03F

Description**Version:****Cordless drill / driver**

- For precise drilling and screw tightening results.
- Electronic speed control for smooth, safe starts to drilling and screw driving; reversible.
- Sturdy metal gearbox for long working life.
- Good weight balance and ergonomics with softgrip inserts for non-tiring continuous work.
- Li-ion batteries with high current capability, single-cell monitoring, and capacity display.

Powerful 12 V / 3 Ah 2-speed gearbox.

Mechanical torque cut-out, in 17 steps, additional drill step.

Standard:

- 2-speed cordless drill/driver.
- Short design of 180 mm.
- Electronic speed control for smooth, safe starts to drilling and screw driving; reversible.
- Sturdy metal gearbox for long working life.

Advantage:

17-step torque adjustment.

Supplied with:

Without battery and without charger.

Supplied with drill chuck, belt clip and transport case.

Note:

See No. 073832 for suitable starter sets (consisting of spare battery and charger).

Technical description

Manufacturer's designation	ABSU 12 SELECT
Quick-clamping chuck range	1 - 10 mm
typical application	Strong
maximum twist drill size Ø in wood	30 mm
Weight	1.2 kg
Battery voltage	12 V
maximum torque soft	14 N·m
maximum twist drill size Ø in steel	10 mm
maximum vibration to EN	< 2.5 m/s ²
suitable battery - supplier / battery type / voltage	Fein type E 12 V
maximum torque hard	20 N·m
Packaging	Carrying case
Motor design	Brushless motor
maximum speed 2nd speed	1300 min ⁻¹
maximum speed 1st speed	400 min ⁻¹
Number of rechargeable batteries contained	0
Type of rechargeable battery	Lithium-ion
Power supply	Rechargeable battery-powered
Suitable for material	wood
Suitable for material	Steel
Type of product	Drill/drivers
USP1	18V, 2-speed
USP2	Quick-release chuck clamping range 1.5-13, in a carrying case

Accessories

Li-ion battery Rechargeable battery type, battery voltage
FE12 V

073837 FE12

Battery starter set Type 9260431701

073832 9260431701