



Three-leg extractor, Type: 3



Order data

Order number	880130 3
GTIN	4021176013546
Item class	83U

Description

Version:

With reversible extraction legs (**for external and internal extraction**). Extraction legs adjustable on cross beam for different workpiece \varnothing . Extraction legs and cross beam of high-quality tool steel; sturdy double-ended spindle (ball end and point end).

Application:

Universally applicable for extracting bearings, discs, gear wheels etc. On model 880100 size 5 the depth of reach can be extended from 400 mm (normal) up to 700 mm by adjusting the legs.

Technical description

Depth of reach up to	200 mm
Internal capacity	180 - 340 mm
Power	10 t
External clamping range	46 - 250 mm
External hexagon drive	27 mm
maximum torque	250 Nm

Number of hooks	3
Weight	9.615 kg
Type of product	Three-leg extractor

Accessories

Spare extractor legs (3 pieces) Type / Clamping depth 3/200 mm	880220 3/200
Pair of spare extractor legs Type / Clamping depth 3/200 mm	880200 3/200
Spare pressure spindle Type 3	880150 3
Extended extractor legs (3 pieces) Type / Clamping depth 4/500 mm	880320 4/500