



Straight die grinder Cordless, Type: 71230262



Order data

| | |
|--------------|-----------------|
| Order number | 077262 71230262 |
| GTIN | |
| Item class | 03F |

Description

Version:

- **Dust-resistant and powerful cordless straight die grinder.**
- **Maintenance-free brushless EC motor with innovative cooling ribs for optimum cooling, including temperature monitoring.**
- **Ideal for every application. Optimum speeds, tailored to a large number of abrasives and materials thanks to stepless, electronic speed pre-selection.**
- **Maximum work progress with FEIN HighPower Li-ion batteries. High-current cells with continuous high current output and 75% higher current than Li-ion batteries.**
- **Extremely smooth cutting action and anti-vibration working thanks to the independently mounted motor, decoupled from the housing, and 4 additional vibration dampers.**
- **Comprehensive user protection: Smooth start-up, restart inhibit, electronic overload protection.**
- **Dust-protected, separate motor electronics in the handle area.**

Long spindle neck. The long, slim neck makes deep plunging into workpieces possible (for example, internal grinding of pipes).

Standard:

- **Maintenance-free brushless EC motor with innovative cooling ribs for optimum cooling, including temperature monitoring.**
- **Maximum work progress with FEIN HighPower Li-ion batteries. High-current cells with permanently high current output and 75% higher current than Li-ion batteries.**
- **Extremely smooth cutting action and anti-vibration work thanks to the independently mounted motor, decoupled from the housing, and 4 additional vibration dampers.**

- **Comprehensive user protection: Smooth start-up, restart inhibit, electronic overload protection.**
- **Dust-protected, separate motor electronics in the handle area.**

Supplied with:

Supplied with 6 mm Ø collet, 1 × 13 AF and 1 × 17 AF spanner, carrying case. **Without battery and charger.** Suitable spare batteries and chargers can be found under No. 073834 – 073845.

Note:

See 073834 ff. for suitable spare batteries and chargers.

Straight die grinders are approved for use with burrs up to a Ø of 12 mm.

Technical description

| | |
|--|--------------------------------|
| maximum collet Ø | 8 mm |
| Battery voltage | 18 V |
| Weight | 1.6 kg |
| electronic speed pre-selection | yes |
| maximum vibration to EN | < 2.5 m/s ² |
| Manufacturer's designation | AGSZ 18-280 LBL Select |
| Speed range | 9000 - 28000 min ⁻¹ |
| Motor design | Brushless |
| suitable battery - supplier / battery type / voltage | Fein type E 12 V |
| suitable battery - supplier / battery type / voltage | Fein type E 18 V |
| Type of rechargeable battery | Lithium-ion |
| Number of rechargeable batteries contained | 0 |
| Power supply | Rechargeable battery-powered |
| Packaging | Carrying case |
| Type of product | Straight die grinder |

Accessories

Li-ion battery Rechargeable battery type, battery voltage
FE12 V

073837 FE12

073837 FE18

Li-ion battery Rechargeable battery type, battery voltage
FE18 V

| | |
|---|----------|
| Collet for straight grinder Collet Ø 8 mm | 077268 8 |
| Collet for straight grinder Collet Ø 6 mm | 077268 6 |