



Cordless hammer drill / driver, Type: 71132364



Order data

Order number	070100 71132364
GTIN	4014586887265
Item class	03F

Description

Version:

2-speed cordless hammer drill with brushless motor.

- **Electronic speed control for smooth, safe starts to drilling and screw driving; reversible.**
- **2-speed all-metal gearbox with selectable hammer drive in metal, stone and masonry.**
- **Multi-stage torque setting.**
- **With QuickIN all-metal drill chuck (120 Nm) with carbide-coated jaws and high clamping forces.**
- **FEIN SafetyCell technology. Protects the battery and the machine against overheating and deep discharge.**

Supplied with:

Supplied with 1 × QuickIN drill chuck (120 Nm), 1 × belt clip, 1 × bit garage, carrying case.

Without battery and without charger.

Note:

See No. 073835 ff. for suitable batteries and chargers.

Packaging: Carrying case

suitable battery - supplier / battery type / voltage: Fein type E 18 V

Manufacturer's designation: ASB 18 Q select

Battery voltage: 18 V

Motor design: Brushless

maximum torque soft: 32 Nm

maximum torque hard: 60 Nm
 maximum speed 1st speed: 0 - 450 rpm

Technical description

typical application	Heavy Duty
Weight	1.3 kg
maximum speed 2nd speed	2000 rpm
Quick-clamping chuck range	1.5 - 13 mm
Manufacturer's designation	ASB 18 Q select
maximum vibration to EN with hammer drill function	13 m/s ²
Battery voltage	18 V
maximum torque hard	60 Nm
maximum vibration to EN without hammer drill function	< 2.5 m/s ²
Motor design	Brushless
maximum speed 1st speed	0 - 450 rpm
maximum twist drill size Ø in concrete	13 mm
suitable battery - supplier / battery type / voltage	Fein type E 18 V
Packaging	Carrying case
maximum twist drill size Ø in steel	13 mm
maximum twist drill size Ø in wood	50 mm
maximum torque soft	32 Nm
Power supply	Rechargeable battery-powered
Type of product	limpact drill /screwdriver

Accessories

Battery charger Type FE50	073845 FE50
Li-ion battery Rechargeable battery type, battery voltage FE18 V	073835 FE18

Li-ion battery Rechargeable battery type, battery voltage FE18 V	073837 FE18
Li-ion battery HighPower Battery type, battery voltage FE18 V	073834 FE18
Accessories for hand-held screwdrivers Quick-In Type 711301	070208 711301
Accessories for hand-held screwdrivers Quick-In Type ANGLE	070208 ANGLE
Accessories for hand-held screwdrivers Quick-In Type CHUCK-SKE	070208 CHUCK-SKE
Accessories for hand-held screwdrivers Quick-In Type CHUCK120	070208 CHUCK120
Accessories for hand-held screwdrivers Quick-In Type CHUCK60	070208 CHUCK60
Accessories for hand-held screwdrivers Quick-In Type HOLESAW	070208 HOLESAW
Accessories for hand-held screwdrivers Quick-In Type INCH12	070208 INCH12
Accessories for hand-held screwdrivers Quick-In Type INCH14	070208 INCH14
Accessories for hand-held screwdrivers Quick-In Type THREAD-SET	070208 THREAD-SET
Offset screwdriving attachment Type OSD2	073920 OSD2
Offset screwdriving attachment Type WB1	073920 WB1
Battery charger Type FE80	073845 FE80