



## Two-leg extractor, Type: 3



### Order data

Order number	880100 3
GTIN	4021176009686
Item class	83U

### Description

#### Version:

With reversible extraction legs (**for external and internal extraction**). Extraction legs adjustable on cross beam for different workpiece  $\varnothing$ . Extraction legs and cross beam of high-quality tool steel; sturdy double-ended spindle (ball end and point end).

#### Application:

Universally applicable for extracting bearings, discs, gear wheels etc. On model 880100 size 5 the depth of reach can be extended from 400 mm (normal) up to 700 mm by adjusting the legs.

### Technical description

Power	8.5 t
Internal capacity	180 - 340 mm
Depth of reach up to	200 mm
External clamping range	65 - 250 mm
maximum torque	300 Nm
Number of hooks	2

External hexagon drive	27 mm
Weight	7.12 kg
Type of product	Two-leg extractor

---

## Accessories

Pair of extended extractor legs Type / Clamping depth 3/300 mm	880300 3/300
Pair of spare extractor legs Type / Clamping depth 3/200 mm	880200 3/200
Spare pressure spindle Type 3	880150 3
Spare extractor legs (3 pieces) Type / Clamping depth 3/200 mm	880220 3/200
Pair of extended extractor legs Type / Clamping depth 4/500 mm	880300 4/500