

**Cordless hammer drill / driver, Type: M12FPD2XK****Order data**

Order number	070110 M12FPD2XK
GTIN	4058546220839
Item class	03L

Description**Version:**

- **Powerful cordless 2-speed hammer drill /screwdriver with multi-stage torque setting.**
- **REDLITHIUM-ION™ Red Li-ion batteries with single-cell monitoring and charge display.**
- **Sturdy metal gearbox for long working life.**
- **FIXTEC metal quick-change chuck with spindle lock.**
- **Handle with Softgrip coating for comfortable use.**
- **LED illumination of the working area.**
- **Brushless POWERSTATE™-motor (not size M18BPD4) for very high efficiency. Very low wear and up to 10 times the working life of standard DC motors.**
- **REDLINK PLUS™ electronics overload protection and power management.**

FUEL™ compact cordless hammer drill/driver with 6-in-1 drilling system. Removable drill chuck system with 3 attachments for maximum flexibility.

Advantage:

6-in-1 drilling solution.

Supplied with:

Supplied with 2 pcs. Li-ion batteries, charger, transport case (HD box) and belt clip, 13 mm quick-change chuck, eccentric attachment, offset screwdriving attachment.

Note:

See No. 073814 – 073816, 073827 and 073840 for suitable batteries and chargers.
The suitable Bluetooth tracking module can be found under 070103 BTT-1.

Technical description

Weight	1.2 kg
maximum speed 2nd speed	1700 min ⁻¹
Motor design	FUEL™
maximum speed 1st speed	0 - 450 min ⁻¹
typical application	Strong
maximum twist drill size Ø in wood	35 mm
Battery voltage	12 V
maximum twist drill size Ø in steel	13 mm
Number of rechargeable batteries contained	2
maximum twist drill size Ø in concrete	13 mm
Type of rechargeable battery	Lithium-ion
maximum torque	37 Nm
suitable battery - supplier / battery type / voltage	Milwaukee type B 12 V
Battery capacity	2 Ah
maximum vibration to EN with hammer drill function	30.8 m/s ²
Packaging	Modular case (HD=Heavy Duty)
Manufacturer's designation	M12FPDXKIT-202X
Quick-clamping chuck range	1.5 - 13 mm
maximum vibration to EN without hammer drill function	<2.5 m/s ²
Power supply	Rechargeable battery-powered
Suitable for material	Steel
Suitable for material	Concrete
Suitable for material	wood
Suitable for material	Masonry
Type of product	limpact drill /screwdriver

Accessories

Li-ion system M4B2/M12B2 Battery type MB12	073814 MB12
Battery charger Type M1218C	073840 M1218C
Battery charger Type M1218FC	073840 M1218FC