



## Two-leg extractor, Type: 30



### Order data

Order number	880100 30
GTIN	4021176010163
Item class	83U

### Description

#### Version:

With reversible extraction legs (**for external and internal extraction**). Extraction legs adjustable on cross beam for different workpiece  $\varnothing$ . Extraction legs and cross beam of high-quality tool steel; sturdy double-ended spindle (ball end and point end).

#### Application:

Universally applicable for extracting bearings, discs, gear wheels etc. On model 880100 size 5 the depth of reach can be extended from 400 mm (normal) up to 700 mm by adjusting the legs.

### Technical description

Depth of reach up to	200 mm
Internal capacity	180 - 440 mm
Power	8.5 t
External clamping range	65 - 350 mm
maximum torque	300 Nm
External hexagon drive	27 mm

Number of hooks	2
Weight	7.525 kg
Type of product	Two-leg extractor

---

## Accessories

Spare pressure spindle Type 3	880150 3
Pair of extended extractor legs Type / Clamping depth 4/500 mm	880300 4/500
Spare extractor legs (3 pieces) Type / Clamping depth 3/200 mm	880220 3/200
Pair of spare extractor legs Type / Clamping depth 3/200 mm	880200 3/200
Pair of extended extractor legs Type / Clamping depth 3/300 mm	880300 3/300