

Ansell**Pair of gloves HyFlex® 11-818, Glove size: 11****Order data**

Order number	094358 11
GTIN	10076490478527
Item class	04P

Description**Version:**

HyFlex® 11-818. With innovative coating for three times longer working life than comparable gloves. Nylon-Spandex backing material with **18 gauge** knitted fabric for the best touch sensitivity for precision work. **Free of silicones and free of latex.** Particularly suitable for the handling of delicate parts, precision assembly of small screws, inserting parts on production lines.

Standard:

EN 388; EN ISO 21420

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Wet grip	good
Glove size	11
Accuracy of fit	very good
silicone-free	no

Touch sensitivity	very good
Heat protection	not available
DMF-free	no
Breathability	very good
Material of coating	Nitrile / PU
Oil grip	good
Series	HyFlex®
Type of glove	Multi-purpose gloves
Protection category	Category II
Clothing standard	Oeko-Tex Standard 100
Contents	12
Glove characteristics	Silicone-free
Glove characteristics	free of latex
Glove characteristics	Suitable for allergy sufferers
Glove characteristics	DMF-free
EN 388	3121A
Backing material	Nylon Spandex
Coating	Nitrile foam
Coating variant	The palms of the hands
Application range	Precision
Length	200 mm
Colour	blue
Weight	16,5 g
Knitted technology	18G
Application	reusable
Material	Nitrile foam
Cut protection class	A
Type of product	Multi-purpose gloves

