



Two-leg extractor, Type: 4



Order data

Order number	880100 4
GTIN	4021176009761
Item class	83U

Description

Version:

With reversible extraction legs (**for external and internal extraction**). Extraction legs adjustable on cross beam for different workpiece \varnothing . Extraction legs and cross beam of high-quality tool steel; sturdy double-ended spindle (ball end and point end).

Application:

Universally applicable for extracting bearings, discs, gear wheels etc. On model 880100 size 5 the depth of reach can be extended from 400 mm (normal) up to 700 mm by adjusting the legs.

Technical description

Internal capacity	200 - 590 mm
External clamping range	80 - 520 mm
Power	12 t
Depth of reach up to	200 mm
Number of hooks	2
maximum torque	400 Nm

External hexagon drive	36 mm
Weight	14 kg
Type of product	Two-leg extractor

Accessories

Hydraulic pressure spindle Type 1	880170 1
Spare pressure spindle Type 4	880150 4
Spare extractor legs (3 pieces) Type / Clamping depth 3/200 mm	880220 3/200
Pair of extended extractor legs Type / Clamping depth 4/500 mm	880300 4/500
Pair of extended extractor legs Type / Clamping depth 3/300 mm	880300 3/300
Pair of spare extractor legs Type / Clamping depth 3/200 mm	880200 3/200