



WOHX 060302 left-hand, W00, Type: P25M

Order data

Order number	268914 P25M
GTIN	4047109055674
Item class	24T

Description

WOHX 060302 left-hand P25M Grade: P25M

Cutting depth a_p : 0.5 - 1.5 mm

Feed f : 0.1 - 0.3 mm/rev.

Cutting speed v_c main application: 120 - 300 m/min

Cutting speed v_c secondary application: 120 - 180 m/min

Technical description

Feed f	0.1 - 0.3 mm/rev.
Cutting speed v_c main application	120 - 300 m/min
Grade	P25M
Cutting conditions	slightly interrupted
Main application	P
Secondary application	M
Cutting depth a_p	0.5 - 1.5 mm
Cutting speed v_c secondary application	120 - 180 m/min

Corner radius	0.2 mm
ISO code indexable insert	WOHX 060302 L
Product name attribute	W00
Rake	6 degrees
Type of product	Indexable insert for turning