


WOHX 08T302 left-hand, W00, Type: BK6425

Order data

Order number	268920 BK6425
GTIN	4047109225756
Item class	24T

Description

WOHX 08T302 left-hand BK6425 Grade: BK6425
 Cutting depth a_p : 0.5 - 1.5 mm
 Feed f : 0.1 - 0.3 mm/rev.
 Cutting speed v_c main application: 120 - 300 m/min
 Cutting speed v_c secondary application: 120 - 180 m/min

Technical description

Corner radius	0.2 mm
Grade	BK6425
Secondary application	M
Main application	P
Cutting conditions	slightly interrupted
Cutting speed v_c secondary application	120 - 180 m/min
Cutting speed v_c main application	120 - 300 m/min
Cutting depth a_p	0.5 - 1.5 mm

Feed f	0.1 - 0.3 mm/rev.
ISO code indexable insert	WOHX 08T302 L
Product name attribute	W00
Rake	12 degrees
Type of product	Indexable insert for turning