

**Garant****Electronics side cutter, small head shape, FW, Overall length: 125mm**

## Order data

Order number	726170 125
GTIN	4045197976468
Item class	71B

## Description

### Version:

Precision machined with slim shape. Cutting edges induction hardened (62 - 64 HRC). Non-reflecting surface, matt shot-blasted with inlaid joint and countersunk screw. Double interchangeable springs for easy operation. **2-component** conductive grips. **Suitable for ESDs**. Cutting edges precision ground.

### Material:

CNC-machined special tool steel for extremely accurate tolerances.

## Technical description

Cutting capacity copper wire up to Ø	0.2 - 1.2 mm
Head width	10 mm
Cutter length	10 mm
overall length	125 mm
electrostatic characteristic	EGB/ESD
Cutting chamfer	fine bevel
Product name attribute	FW
Type of product	Cutting pliers

