

Garant**Electronics side cutter, standard head shape, FW, Overall length: 125mm**

Order data

Order number	726210 125
GTIN	4045197976482
Item class	71B

Description

Version:

Precision machined with slim shape. Cutting edges induction hardened (62 - 64 HRC). Non-reflecting surface, matt shot-blasted with inlaid joint and countersunk screw. Double interchangeable springs for easy operation. **2-component** conductive grips. **Suitable for ESDs.** Cutting edges precision ground.

Material:

CNC-machined special tool steel for extremely accurate tolerances.

Technical description

Head width	12 mm
Cutting capacity copper wire up to Ø	0.2 - 1.6 mm
overall length	125 mm
Cutter length	11.5 mm
electrostatic characteristic	EGB/ESD
Cutting chamfer	fine bevel
Product name attribute	FW
Type of product	Cutting pliers

