

**Garant****Electronics side cutter, standard head shape, SFW, Overall length: 125mm**

## Order data

Order number	726215 125
GTIN	4045197976499
Item class	71B

## Description

**Version:**

Precision machined with slim shape. Cutting edges induction hardened (62 - 64 HRC). Non-reflecting surface, matt shot-blasted with inlaid joint and countersunk screw. Double interchangeable springs for easy operation. **2-component** conductive grips. **Suitable for ESDs**. Cutting edges precision ground.

**Material:**

CNC-machined special tool steel for extremely accurate tolerances.

## Technical description

Cutter length	11.5 mm
Cutting capacity copper wire up to Ø	0.2 - 1.6 mm
Head width	12 mm
overall length	125 mm
electrostatic characteristic	EGB/ESD
Cutting chamfer	very fine bevel
Product name attribute	SFW
Type of product	Cutting pliers

