

Garant

Electronics side cutter, pointed head, hollowed jaws, kW, Overall length: 125mm



Order data

| | |
|--------------|---------------|
| Order number | 726255 125 |
| GTIN | 4045197976611 |
| Item class | 71B |

Description

Version:

Precision machined with slim shape. Cutting edges induction hardened (62 - 64 HRC). Non-reflecting surface, matt shot-blasted with inlaid joint and countersunk screw. Double interchangeable springs for easy operation. **2-component** conductive grips. **Suitable for ESDs.** Cutting edges precision ground.

Material:

CNC-machined special tool steel for extremely accurate tolerances.

Technical description

| | |
|--------------------------------------|----------------|
| Cutting capacity copper wire up to Ø | 0.1 - 1 mm |
| Cutter length | 10 mm |
| Head width | 10 mm |
| overall length | 125 mm |
| electrostatic characteristic | EGB/ESD |
| Cutting chamfer | without bevel |
| Product name attribute | kW |
| Type of product | Cutting pliers |

