

Garant**Electronics side cutter, pointed head, kW, Overall length: 125mm**

Order data

Order number	726250 125
GTIN	4045197976604
Item class	71B

Description

Version:

Precision machined with slim shape. Cutting edges induction hardened (62 - 64 HRC). Non-reflecting surface, matt shot-blasted with inlaid joint and countersunk screw. Double interchangeable springs for easy operation. **2-component** conductive grips. **Suitable for ESDs.** Cutting edges precision ground.

Material:

CNC-machined special tool steel for extremely accurate tolerances.

Technical description

overall length	125 mm
Cutter length	10 mm
Cutting capacity copper wire up to Ø	0.1 - 1 mm
Head width	10 mm
electrostatic characteristic	EGB/ESD
Cutting chamfer	without bevel
Product name attribute	kW
Type of product	Cutting pliers

