



Digital caliper "Ultra Light", Measuring range: 600mm



Order data

Order number	415542 600
GTIN	7640125712414
Item class	46A

Description

Version:

Extremely light-weight caliper. The measuring beam is of aluminium hollow section, very high stiffness due to four hardened and ground steel rods. Very large LCD display, character height 20mm. External jaws of hardened stainless steel with titanium coating. Measuring force limitation for consistent measuring force (7.5 – 11.5 N). Exchangeable measuring tips for inside measurements. Functions: Preset, Max/Min, Delta, display of the upper and lower tolerance limits.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

1 battery No. 081560 size CR2032, 2 pins for internal measurements on the jaw.

Optional extras:

Data cable No. 498948.

Technical description

Standard	Manufacturer's standard
Error limit	0.04 mm
Calibration	A1
Number of batteries contained	1
Scale divisions	0.01 mm
Measuring range	0 - 600 mm

Reversible reading	mm / inch
Jaw length	202 mm
Digit height LCD display	20 mm
Scale divisions	0.0005 in
Weight	1.5 kg
Article no of the battery / rechargeable battery fitted	081560 CR2032
IP Index of Protection	IP 67
Power supply	Battery-powered
Interface	RS232C interface
Interface	USB interface
Measurement technology	digital
Type of product	Universal calipers

Services

CalibrationCalipers / depth gauges maximum measuring range 1000 mm	021000 1000
DAkkS calibrationCalipers / depth gauges maximum measuring range 1000 mm	021010 1000

Accessories

Button cell / special battery Battery type CR2032	081560 CR2032
---	---------------