

Garant**Soft-faced hammer with rubber inserts, black, Housing Ø / material: 30Gmm****Order data**

Order number	752500 30G
GTIN	4045197976581
Item class	71D

Description**Version:**

Soft-faced hammer with dead-blow absorption and removable functional inserts to allow use as a normal soft-faced hammer. Sturdy two-piece precision cast housing of high-quality heat treatable steel. Inserts can be combined and exchanged. With handle of American hickory wood, varnished.

Application:

For straightening or aligning components on machine tables or for application of light impacts in assembly work.

Spare part:

Spare handle available under No. 752530 and spare inserts under No. 752540– 752560.

Technical description

Overall length	300 mm
Handle length	260 mm
Head length with inserts	92 mm
Weight without inserts	228 g
Striking face Ø of the inserts	30 mm
Colour	black
dead-blow	yes
Inserts can be combined	yes

Type of product

Hammer

Accessories

Hickory hammer handle for body Ø 30 mm

752530 30

Rubber insert, soft for soft-faced hammer 30

752540 30

Plastic insert, medium hard for soft-faced hammer 30

752550 30

Nylon insert, hard for soft-faced hammer 30

752560 30