

Garant**Soft-faced hammer with rubber inserts, black, Housing Ø / material: 60Gmm****Order data**

Order number	752500 60G
GTIN	4045197977410
Item class	71D

Description**Version:**

Soft-faced hammer with dead-blow absorption and removable functional inserts to allow use as a normal soft-faced hammer. Sturdy two-piece precision cast housing of high-quality heat treatable steel. Inserts can be combined and exchanged. With handle of American hickory wood, varnished.

Application:

For straightening or aligning components on machine tables or for application of light impacts in assembly work.

Spare part:

Spare handle available under No. 752530 and spare inserts under No. 752540– 752560.

Technical description

Overall length	410 mm
Handle length	335 mm
Weight without inserts	940 g
Head length with inserts	149 mm
Striking face Ø of the inserts	60 mm
Colour	black
dead-blow	yes
Inserts can be combined	yes

Type of product

Hammer

Accessories

Plastic insert, medium hard for soft-faced hammer 60

752550 60

Nylon insert, hard for soft-faced hammer 60

752560 60

Rubber insert, soft for soft-faced hammer 60

752540 60

Hickory hammer handle for body Ø 60 mm

752530 60