

**Garant**
**Soft-faced hammer with rubber inserts, black, Housing Ø / material: 40Gmm**

**Order data**

Order number	752500 40G
GTIN	4045197976598
Item class	71D

**Description**
**Version:**

Soft-faced hammer with dead-blow absorption and removable functional inserts to allow use as a normal soft-faced hammer. Sturdy two-piece precision cast housing of high-quality heat treatable steel. Inserts can be combined and exchanged. With handle of American hickory wood, varnished.

**Application:**

For straightening or aligning components on machine tables or for application of light impacts in assembly work.

**Spare part:**

Spare handle available under No. 752530 and spare inserts under No. 752540– 752560.

**Technical description**

Overall length	330 mm
Striking face Ø of the inserts	40 mm
Weight without inserts	418 g
Head length with inserts	116 mm
Handle length	275 mm
Colour	black
dead-blow	yes
Inserts can be combined	yes

Type of product

Hammer

---

**Accessories**

Nylon insert, hard for soft-faced hammer 40

752560 40

Plastic insert, medium hard for soft-faced hammer 40

752550 40

Rubber insert, soft for soft-faced hammer 40

752540 40

Hickory hammer handle for body Ø 40 mm

752530 40