

**Garant****Soft-faced hammer with plastic inserts, red, Housing Ø / material: 40Gmm****Order data**

|              |               |
|--------------|---------------|
| Order number | 752510 40G    |
| GTIN         | 4045197977007 |
| Item class   | 71D           |

**Description****Version:**

Soft-faced hammer with dead-blow absorption and removable functional inserts to allow use as a normal soft-faced hammer. Sturdy two-piece precision cast housing of high-quality heat treatable steel. Inserts can be combined and exchanged. With handle of American hickory wood, varnished.

**Application:**

For straightening or aligning components on machine tables or for application of light impacts in assembly work.

**Spare part:**

Spare handle available under No. 752530 and spare inserts under No. 752540– 752560.

**Technical description**

|                                |        |
|--------------------------------|--------|
| Striking face Ø of the inserts | 40 mm  |
| Head length with inserts       | 116 mm |
| Weight without inserts         | 418 g  |
| Handle length                  | 275 mm |
| Overall length                 | 330 mm |
| Colour                         | red    |
| dead-blow                      | yes    |
| Inserts can be combined        | yes    |

Type of product

Hammer

---

**Accessories**

Plastic insert, medium hard for soft-faced hammer 40

752550 40

Hickory hammer handle for body Ø 40 mm

752530 40

Nylon insert, hard for soft-faced hammer 40

752560 40

Rubber insert, soft for soft-faced hammer 40

752540 40