

Garant**Soft-faced hammer with nylon inserts, natural, Housing Ø / material: 50Gmm****Order data**

Order number	752520 50G
GTIN	4045197978059
Item class	71D

Description**Version:**

Soft-faced hammer with dead-blow absorption and removable functional inserts to allow use as a normal soft-faced hammer. Sturdy two-piece precision cast housing of high-quality heat treatable steel. Inserts can be combined and exchanged. With handle of American hickory wood, varnished.

Application:

For straightening or aligning components on machine tables or for application of light impacts in assembly work.

Spare part:

Spare handle available under No. 752530 and spare inserts under No. 752540– 752560.

Technical description

Overall length	380 mm
Weight without inserts	785 g
Head length with inserts	138 mm
Striking face Ø of the inserts	50 mm
Handle length	310 mm
Colour	natural
dead-blow	yes
Inserts can be combined	yes

Type of product

Hammer

Accessories

Nylon insert, hard for soft-faced hammer 50

752560 50

Plastic insert, medium hard for soft-faced hammer 50

752550 50

Hickory hammer handle for body Ø 50 mm

752530 50

Rubber insert, soft for soft-faced hammer 50

752540 50