

Garant**Soft-faced hammer with nylon inserts, natural, Housing Ø / material: 40Gmm****Order data**

Order number	752520 40G
GTIN	4045197978042
Item class	71D

Description**Version:**

Soft-faced hammer with dead-blow absorption and removable functional inserts to allow use as a normal soft-faced hammer. Sturdy two-piece precision cast housing of high-quality heat treatable steel. Inserts can be combined and exchanged. With handle of American hickory wood, varnished.

Application:

For straightening or aligning components on machine tables or for application of light impacts in assembly work.

Spare part:

Spare handle available under No. 752530 and spare inserts under No. 752540– 752560.

Technical description

Head length with inserts	116 mm
Overall length	330 mm
Weight without inserts	418 g
Handle length	275 mm
Striking face Ø of the inserts	40 mm
Colour	natural
dead-blow	yes
Inserts can be combined	yes

Type of product

Hammer

Accessories

Hickory hammer handle for body Ø 40 mm

752530 40

Rubber insert, soft for soft-faced hammer 40

752540 40

Plastic insert, medium hard for soft-faced hammer 40

752550 40

Nylon insert, hard for soft-faced hammer 40

752560 40