

**Garant****Soft-faced hammer with nylon inserts, natural, Housing Ø / material: 60Gmm****Order data**

Order number	752520 60G
GTIN	4045197978066
Item class	71D

**Description****Version:**

Soft-faced hammer with dead-blow absorption and removable functional inserts to allow use as a normal soft-faced hammer. Sturdy two-piece precision cast housing of high-quality heat treatable steel. Inserts can be combined and exchanged. With handle of American hickory wood, varnished.

**Application:**

For straightening or aligning components on machine tables or for application of light impacts in assembly work.

**Spare part:**

Spare handle available under No. 752530 and spare inserts under No. 752540– 752560.

**Technical description**

Striking face Ø of the inserts	60 mm
Overall length	410 mm
Handle length	335 mm
Head length with inserts	149 mm
Weight without inserts	940 g
Colour	natural
dead-blow	yes
Inserts can be combined	yes

Type of product

Hammer

---

**Accessories**

Hickory hammer handle for body Ø 60 mm

752530 60

Nylon insert, hard for soft-faced hammer 60

752560 60

Plastic insert, medium hard for soft-faced hammer 60

752550 60

Rubber insert, soft for soft-faced hammer 60

752540 60