

Garant**Soft-faced hammer with plastic inserts, red, Housing Ø / material: 50Gmm****Order data**

Order number	752510 50G
GTIN	4045197977014
Item class	71D

Description**Version:**

Soft-faced hammer with dead-blow absorption and removable functional inserts to allow use as a normal soft-faced hammer. Sturdy two-piece precision cast housing of high-quality heat treatable steel. Inserts can be combined and exchanged. With handle of American hickory wood, varnished.

Application:

For straightening or aligning components on machine tables or for application of light impacts in assembly work.

Spare part:

Spare handle available under No. 752530 and spare inserts under No. 752540– 752560.

Technical description

Handle length	310 mm
Overall length	380 mm
Head length with inserts	138 mm
Weight without inserts	785 g
Striking face Ø of the inserts	50 mm
Colour	red
dead-blow	yes
Inserts can be combined	yes

Type of product

Hammer

Accessories

Hickory hammer handle for body Ø 50 mm

752530 50

Nylon insert, hard for soft-faced hammer 50

752560 50

Rubber insert, soft for soft-faced hammer 50

752540 50

Plastic insert, medium hard for soft-faced hammer 50

752550 50