

**Cordless hammer drill / driver, Type: GSB1821****Order data**

| | |
|--------------|----------------|
| Order number | 070105 GSB1821 |
| GTIN | 3165140979436 |
| Item class | 03B |

Description**Version:**

Bosch cordless hammer drill / driver for very heavy-duty screwdriving, drilling and hammer drilling applications.

- **Electronic Cell Protection (ECP) protects the battery against overheating and deep discharge.**
- **Electronic Motor Protection (EMP) protects the motor against overloading.**
- **Mechanical multi-stage torque cut-out.**
- **Handy belt clip (not 070104).**
- **Integral LED light, battery charge indicator.**
- **Quick-clamping drill chuck.**

Robust cordless screwdriver with powerful DC motor. With motor brake.

Advantage:

Electronic Motor Protection.

Supplied with:

Supplied with 2 pcs. 18V / 2.0 Ah Li-ion battery, charger and L-BOXX.

Note:

See from No. 073851 and 073866 for suitable replacement batteries and chargers.

Technical description

| | |
|---|------------------------------|
| maximum vibration to EN without hammer drill function | 2.5 m/s ² |
| Battery voltage | 18 V |
| maximum twist drill size Ø in steel | 10 mm |
| maximum speed 2nd speed | 1800 min ⁻¹ |
| Manufacturer's designation | GSB 18V-21 |
| Packaging | Modular case (L-Boxx) |
| maximum torque hard | 55 Nm |
| suitable battery - supplier / battery type / voltage | Bosch 18 V |
| Weight | 1.5 kg |
| maximum torque soft | 21 Nm |
| typical application | Medium |
| Quick-clamping chuck range | 1.5 - 13 mm |
| maximum twist drill size Ø in wood | 35 mm |
| Battery capacity | 2 Ah |
| maximum speed 1st speed | 0 - 480 min ⁻¹ |
| Motor design | 4-pole DC motor |
| Number of rechargeable batteries contained | 2 |
| Type of rechargeable battery | Lithium-ion |
| Power supply | Rechargeable battery-powered |
| Suitable for material | Stone |
| Suitable for material | Steel |
| Suitable for material | Concrete |
| Suitable for material | Masonry |
| Type of product | limpact drill /screwdriver |

Accessories

| | |
|--|------------|
| Li-ion battery Battery type, battery voltage B18 V | 073851 B18 |
|--|------------|

| | |
|---|-----------------|
| Battery charger Type 1880CV | 073866 1880CV |
| Wireless charging starter set Type GAL1830W | 073862 GAL1830W |