

**Pair of gloves with raised dots, Glove size: 8****Order data**

Order number	094287 8
GTIN	4045197977526
Item class	02H

Description**Version:**

Gloves with additional raised dots for improved security of grip.

Glove with water-based PU nitrile foam coating for good dexterity and grip in dry and slightly damp or oil conditions. Good fit and touch sensitivity due to innovative knitted technology with polyamide-Lycra fibres. **Free of DMF.** Particularly suitable for assembly of small components, goods receiving and dispatch and maintenance work.

Standard:

EN 388; EN ISO 21420

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Glove size	8
Type of glove	Multi-purpose gloves
Protection category	Category II
Clothing standard	Oeko-Tex Standard 100

Contents	12
Glove characteristics	DMF-free
Glove characteristics	Suitable for allergy sufferers
EN 388	4131X
Backing material	Lycra®, polyamide
Coating	water-based PU/nitrile
Coating variant	The palms of the hands
Application range	All-round
Length	255 mm
Colour	black / grey
Knitted technology	15G
AQL	G-II 1.0 for critical, G-II 2.5 for major, G-II 4.0 for minor.
Application	reusable
Type of product	Multi-purpose gloves