

**LESSMANN®**  
THE GERMAN BRUSH COMPANY**Cup brush Brass-coated steel wire 0.30 mm, Brush Ø D1: 60mm****Order data**

Order number	573300 60
GTIN	4017359147290
Item class	57L

**Description****Version:**

Waved wire firmly crimped into the steel body. For use on angle grinders and on stationary machines.

The high-tensile steel wire is coated with a thin layer of brass.

With **M14 internal thread**. With **M14 internal thread**.

**Application:**

Very well suited for brushing surfaces, deburring, removing rust, polishing, removing paint, primer, varnish, scale etc.

**Technical description**

Bristle thickness	0.3 mm
Length of brush section H <sub>1</sub>	20 mm
Brush Ø D <sub>1</sub>	65 mm
maximum speed	12000 min <sup>-1</sup>
Thread M	M14
Brush material	Steel wire

Type of product

Cup brush