



Side cutter, chrome-plated, Overall length: 160mm



Order data

Order number	725265 160
GTIN	3662424076541
Item class	73R

Description

Version:

Jaws chrome-plated with thick-walled grips. **Plastic opening spring for reduced operator fatigue.** Cutting edges additionally induction hardened (approx. 62 HRC).

Standard:

DIN ISO 5749

Material:

Chrome vanadium steel, drop-forged and oil-hardened.

Technical description

overall length	160 mm
Cutting capacity piano wire up to Ø	1.8 mm
Cutting capacity hard wire up to Ø	2 mm
Standard	DIN ISO 5749
Handle	Heavy-duty grip
Manufacturing process	Cutting edges induction hardened (approx. 62 HRC)
Material	Chromium vanadium steel
Surface	chrome-plated

Heavy-duty diagonal side cutter	no
with selectable return spring	no
with return spring	yes
Type of product	Cutting pliers