

**Electronics side cutter, mirror-polished, round head, FW, Overall length: 115mm****Order data**

| | |
|--------------|---------------|
| Order number | 726429 115 |
| GTIN | 4003773018568 |
| Item class | 73F |

Description**Version:**

Mirror polished, therefore no faults in the circuit due to peeling chrome plate. Sturdy box joint with zero play. Low-friction double spring for smooth and gentle opening.

Plastic coated handles.

Application:

For making precision cuts, e.g. in electronics and precision mechanisms.

Standard:

DIN ISO 9654

Material:

Ball-bearing steel, cutting edges induction hardened.

Technical description

| | |
|---|--------------|
| Head width | 11 mm |
| Cutter length | 14 mm |
| Cutting capacity medium hard wire up to Ø | 0.3 - 1.2 mm |
| Cutting capacity hard wire up to Ø | 0.3 - 0.6 mm |
| overall length | 115 mm |
| Cutting capacity copper wire up to Ø | 0.3 - 1.6 mm |
| Cutting chamfer | fine bevel |

| | |
|------------------------|---|
| Material | Ball bearing steel |
| Head shape | round |
| Standard | DIN ISO 9654 |
| Handle | plastic coated |
| Manufacturing process | Cutting edges induction hardened (approx. 62 HRC) |
| Surface | mirror polished |
| Product name attribute | FW |
| with return spring | yes |
| Type of product | Cutting pliers |