



Three-leg extractor with pre-adjustable clamping range, Type: 1



Order data

Order number	880950 1
GTIN	4021176006616
Item class	83U

Description

Version:

Powerful extractor with high clamping force and excellent clamping. Using the adjustment wrench, the symmetrical clamping legs are easily set to the necessary spread. The part to be extracted is **positively gripped**, the **gripper jaws** cannot **jump or slip**.

For external extraction only.

Application:

For extracting tightly seized ball bearings, gear wheels, pulleys and similar parts.

Technical description

Power	8 t
External clamping range	20 - 100 mm
Depth of reach up to	100 mm
External hexagon drive	17 mm
maximum torque	180 Nm
Number of hooks	3

Weight	1.24 kg
Type of product	Three-leg extractor