



**Electronics side cutter, mirror-polished, round head with wire holder, FW,  
Overall length: 115mm**



## Order data

Order number	726433 115
GTIN	4003773043768
Item class	73F

## Description

**Version:**

Mirror polished, therefore no faults in the circuit due to peeling chrome plate. Sturdy box joint with zero play. Low-friction double spring for smooth and gentle opening.  
Handles with multi-component coating.

**Application:**

For making precision cuts, e.g. in electronics and precision mechanisms.

**Standard:**

DIN ISO 9654

**Material:**

Ball-bearing steel, cutting edges induction hardened.

## Technical description

Head width	11 mm
Cutting capacity copper wire up to Ø	0.3 - 1.6 mm
Cutting capacity hard wire up to Ø	0.3 - 0.6 mm
overall length	115 mm
Cutter length	14 mm
Cutting capacity medium hard wire up to Ø	0.3 - 1.2 mm
Cutting chamfer	fine bevel

Material	Ball bearing steel
Head shape	round
Standard	DIN ISO 9654
Handle	Multi-component covering
Manufacturing process	Cutting edges induction hardened (approx. 62 HRC)
Surface	mirror polished
Product name attribute	FW
with return spring	yes
Type of product	Cutting pliers