

**Electronics flat-nosed pliers, Overall length: 115mm****Order data**

Order number	727189 115
GTIN	4003773016694
Item class	73F

Description**Version:**

Mirror polished, therefore no faults in the circuit due to peeling chrome plate. Precision box joint. Low-friction double spring for smooth and gentle opening. Gripping faces ground smooth. Edges carefully deburred.

Plastic coated handles.

Application:

For precision assembly work, e.g. in electronics and precision mechanisms.

Standard:

DIN ISO 9655

Material:

Ball-bearing steel, oil quenched.

Note:

Further versions available on request.

Technical description

overall length	115 mm
Jaw length	22.5 mm
Type of jaws	inside ground smooth
Head width	9.5 mm
Jaw design	flat, straight
Standard	DIN ISO 9655

Handle	plastic coated
Material	Ball bearing steel
Surface	mirror polished
with return spring	yes
Type of product	Flat-nose pliers