



Three-leg extractor with pre-adjustable clamping range, Type: 2



Order data

Order number	880950 2
GTIN	4021176006791
Item class	83U

Description

Version:

Powerful extractor with high clamping force and excellent clamping. Using the adjustment wrench, the symmetrical clamping legs are easily set to the necessary spread. The part to be extracted is **positively gripped**, the **gripper jaws** cannot **jump or slip**.

For external extraction only.

Application:

For extracting tightly seized ball bearings, gear wheels, pulleys and similar parts.

Technical description

External clamping range	35 - 150 mm
Depth of reach up to	125 mm
Power	9 t
maximum torque	190 Nm
Number of hooks	3
External hexagon drive	19 mm

Weight	1.72 kg
Type of product	Three-leg extractor