



Two-leg extractor with quick adjustment, Type: 3



Order data

Order number	880400 3
GTIN	4021176645198
Item class	83U

Description

Version:

With knurled grip for **quick loosening and moving** of the extractor legs **without additional tools**.

Application:

Universally capable of extracting bearings, gear wheels etc. **Can be used as external and internal extractor.**

Technical description

Power	8.5 t
External clamping range	65 - 250 mm
Internal capacity	180 - 340 mm
Depth of reach up to	200 mm
Number of hooks	2
External hexagon drive	27 mm

maximum torque	300 Nm
Weight	7.05 kg
Type of product	Two-leg extractor