



Hydraulic ram, Type: 3



Order data

Order number	881800 3
GTIN	4021176924408
Item class	83U

Description

Version:

Steel body with hydraulic mechanism and automatic return. Easy handling: the ram is used between extractor spindle and shaft. Clamp ram with extractor spindle and tighten ram spindle (hydraulics come into effect). If the travel is insufficient, release the ram spindle and repeat the procedure.

Application:

For increasing the power of mechanical extractors from Size 3. Even tightly seized parts can easily be freed.

Technical description

maximum permissible extraction force	300 kN
Stroke	7 mm
Construction height	113 mm
maximum permissible torque	40 Nm
Body Ø	80 mm
Ram cylinder Ø	39.5 mm
Type of product	Hydraulic ram

