



Two-leg extractor with quick adjustment, Type: 30



Order data

Order number	880400 30
GTIN	4021176645273
Item class	83U

Description

Version:

With knurled grip for **quick loosening and moving** of the extractor legs **without additional tools**.

Application:

Universally capable of extracting bearings, gear wheels etc. **Can be used as external and internal extractor.**

Technical description

External clamping range	65 - 350 mm
Internal capacity	180 - 440 mm
Power	8.5 t
Depth of reach up to	200 mm
External hexagon drive	27 mm
maximum torque	300 Nm

Number of hooks	2
Weight	7.51 kg
Type of product	Two-leg extractor