

RENISHAW**Stylus, ruby ball Length 10/11 mm, Contact point Ø D: 2,5mm****Order data**

Order number	494220 2,5
GTIN	2050001957214
Item class	49F

Description**Version:**

Ruby-tipped probe with M2 connection thread

Note:

Further styli with other sizes and shank types available on request.

Technical description

Length L	10 mm
Contact point Ø D	2.5 mm
Material of shank	Steel
Shank Ø S	1 mm
effective working length	6.5 mm
Weight	0.3 g
Connection thread	M2
Material of point	Ruby
Type of product	Probes