

FACOM.

Internal / external extractor, Type: 2



Order data

Order number	880850 2
GTIN	3148519884357
Item class	83H

Description

Version:

With two sets of exchangeable extractor legs for **internal and external extraction**, allowing either 2 or 3 extractor legs to be used.

- · Secure: Full extractor leg locking with a knurled screw.
- · Practical: Extractor legs can easily be added or removed.
- · Automatic: Self-tightening and self-centring.
- · Spindle nose: With force limiter the shear pin will fracture at overload.

Supplied with:

Basic body with spindle and 3 internal and external extractor legs each.

External clamping range: 10 - 180 mm

Internal capacity: 50 - 170 mm Depth of reach up to: 190 mm

Technical description

Depth of reach up to	190 mm
External clamping range	10 - 180 mm
Internal capacity	50 - 170 mm

