



Internal / external extractor, Type: 2



Order data

Order number	880850 2
GTIN	3148519884357
Item class	83H

Description

Version:

With two sets of exchangeable extractor legs for **internal and external extraction**, allowing either 2 or 3 extractor legs to be used.

- **Secure: Full extractor leg locking with a knurled screw.**
- **Practical: Extractor legs can easily be added or removed.**
- **Automatic: Self-tightening and self-centring.**
- **Spindle nose: With force limiter - the shear pin will fracture at overload.**

Supplied with:

Basic body with spindle and 3 internal and external extractor legs each.

Technical description

Depth of reach up to	190 mm
External clamping range	10 - 180 mm
Internal capacity	50 - 170 mm
Type of product	Three-leg extractor

