



## Three-leg extractor with pre-adjustable clamping range, Type: 4



### Order data

Order number	880960 4
GTIN	4021176850509
Item class	83U

### Description

#### Version:

Powerful extractor with high clamping force and excellent clamping. Using the adjustment wrench, the symmetrical clamping legs are easily set to the necessary spread. The part to be extracted is **positively gripped**, the **gripper jaws** cannot **jump or slip**.

For external **and** internal extraction.

#### Application:

For extracting tightly seized ball bearings, gear wheels, pulleys and similar parts.

### Technical description

Depth of reach up to	225 mm
Clamping depth	50 mm
Power	10 t
External clamping range	20 - 250 mm
Internal capacity	225 - 325 mm
External hexagon drive	27 mm

Number of hooks	3
maximum torque	300 Nm
Weight	11.99 kg
Type of product	Three-leg extractor