



Low-profile shoe, black/blue VD PRO 1100 SF ESD, S1P XB, EU shoe size: 40



Order data

Order number	092556 40
GTIN	4044348521120
Item class	09C

Description

Version:

VARIO DYNAMICS® PRO range of safety shoes. VARIO Multiflex® technology for less shoe weight.

- **Upper made of a very light microfibre.**
- **Breathable functional lining.**
- **TPU Athletic ESD outer sole.**
- **Real leather insole.**
- **ERGO-SOFT ESD comfort mid-sole inlay.**
- **Protection against electrostatic discharge (ESD).**

Low-profile shoe with large area ventilation structure. Dust tongue, toe protection.

Low-profile shoe of seam-free construction. Dust tongue, appliques on the upper part of the shoe.

SF range with textile penetration protection. Without **SECURA VARIO® heel shock absorption.**

Standard:

EN ISO 20345:2011 S1 P SRC

Einlagenversorgung baumustergeprüft nach DGUV Regel 191.

Note:

Standard version NB, see No. 092555.

electrostatic characteristic: EGB/ESD

Protection class: S1P

Material of protective toe-cap: Aluminium

Puncture resistance: Tekstil

Standard: Inlay type-tested according to DGUV regulation 191

Technical description

Material of protective toe-cap	Aluminium
Protection class	S1P
Standard	Inlay type-tested according to DGUV regulation 191
EU shoe size	40
Colour	black / blue
Puncture resistance	Tekstil
Gender	Gentlemen's
electrostatic characteristic	EGB/ESD
Type of product	Safety shoes