



Shoe, black VD PRO 3500 SF ESD, S3 NB, EU shoe size: 40



Order data

Order number	092580 40
GTIN	4044348572528
Item class	09C

Description

Version:

Safety shoe with VARIO Multiflex® technology for less shoe weight.

- **Upper material of ultra-light and smooth micro-fibres.**
- **Breathable functional lining.**
- **Real leather insole.**
- **ERGO-SOFT ESD comfort mid-sole inlay.**
- **Protection against electrostatic discharge (ESD).**

VARIO DYNAMICS PRO SF range safety shoes with **textile penetration protection**. Without SECURA VARIO® heel shock absorption.

- **TPU Athletics ESD outer sole, black.**

Shoe of seam-free construction. Dust tongue, appliques on the upper part of the shoe.

Standard:

EN ISO 20345:2011 S3 SRC

Einlagenversorgung baumustergeprüft nach DGUV Regel 191.

Note:

Wide version XB, see No. 092581.

electrostatic characteristic: EGB/ESD

Protection class: S3

Material of protective toe-cap: Aluminium

Puncture resistance: Tekstil

Cold insulation: down to -20°C

Standard: Inlay type-tested according to DGUV regulation 191

Technical description

Cold insulation	down to -20°C
Protection class	S3
EU shoe size	40
Colour	black
Standard	Inlay type-tested according to DGUV regulation 191
Puncture resistance	Tekstil
Material of protective toe-cap	Aluminium
Gender	Unisex
electrostatic characteristic	EGB/ESD
Type of product	Safety shoes