

Garant**Cleaningpoint empty, Type: M****Order data**

Order number	987101 M
GTIN	4045197977588
Item class	91M

Description**Version:**

Distortion-free body of sheet metal. Centre partition with \square 9x9 mm holes at 37 mm pitch. 4 swivel castors (\varnothing 100 mm) with parking brake and 2 large push handles with Haptoprene coating ensure stability and safe handling.

Colour:

Two-tone **powder-coated**, silver combined with RAL 7016 anthracite.

Hoffmann perforated panel grid interval: 9x9 mm

Height: 1850 mm

Width: 725 mm

Depth: 634 mm

Body depth: 524 mm

Usable height: 1650 mm

Usable width: 720 mm

Technical description

Body depth	524 mm
Width	725 mm

Usable height	1650 mm
Height	1850 mm
Depth	634 mm
Weight	65 kg
Usable width	720 mm
Type	M
Hoffmann perforated panel grid interval	9×9 mm
Type of product	Cleaning station