

Garant**Cleaningpoint empty, Type: S****Order data**

Order number	987101 S
GTIN	4045197977571
Item class	91M

Description**Version:**

Distortion-free body of sheet metal. Centre partition with \square 9x9 mm holes at 37 mm pitch.

Colour:

Two-tone **powder-coated**, silver combined with RAL 7016 anthracite.

Hoffmann perforated panel grid interval: 9x9 mm

Height: 1700 mm

Width: 725 mm

Depth: 634 mm

Body depth: 524 mm

Usable height: 1650 mm

Usable width: 720 mm

Technical description

Usable width	720 mm
Depth	634 mm
Height	1700 mm

Body depth	524 mm
Type	S
Usable height	1650 mm
Weight	63 kg
Width	725 mm
Hoffmann perforated panel grid interval	9×9 mm
Type of product	Cleaning station