

**Angle grinder GWS, Type: 9-125S****Order data**

Order number	077109 9-125S
GTIN	3165140923118
Item class	03C

Description**Version:**

Handy compact angle grinder with a narrow handle circumference.

- **Strong 900 W motor for fast work, high overload capacity, durability.**
- **With speed-control electronics, ideal for instance for grinding stainless steel.**

Supplied with:

Supplied with torsion-resistant protective hood, clamping set, additional handle.

Technical description

Power consumption	900 W
maximum cutting depth	34 mm
Manufacturer's designation	GWS 9-125 S
maximum vibration to EN	6 m/s ²
maximum disc Ø	125 mm
Special features	Electronic speed control.
Weight	1.9 kg
Restart block	yes
Speed range	2800 - 11000 min ⁻¹
Power supply	Mains operated

Type of product

Angle grinder